

# SOLBERG® RE-HEALING™ RF3X6% FREEZE PROTECTED ATC™ FOAM CONCENTRATE



## TYPICAL PHYSICAL PROPERTIES

AT 77 °F (25 °C)

**Appearance:** Brown liquid

**Freezing Point:** -2°F (-18°C)  
(No quality loss after thawing)

**Maximum Storage Temp:** 122°F (50°C)

**pH:** 7.0 - 8.5

**Refractive Index:** 1.3840 - 1.4140

**Specific Gravity:** 1.080 - 1.116

**Viscosity:** 4900 - 6700 cP\*

**Sediments:** < 0.05%

\*Brookfield Viscometer Spindle #4,  
Speed 30 rpm

## APPLICATION

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate is intended for use on Class B hydrocarbon or polar solvent fuel fires. The foam can be used to prevent re-ignition of a liquid spill and control hazardous vapors. On Class A fuels, SOLBERG RE-HEALING RF3x6 FP ATC foam will improve extinguishment in deep-seated fires. Foam discharge devices such as air aspirating, as well as, non-air aspirating equipment, including standard sprinkler heads, can be used to obtain maximum results. The product is mixed 3 parts foam concentrate to 97 parts water for hydrocarbon fuels or 6 parts foam concentrate to 94 parts water for polar solvent fuels. It may also be used as a pre-mix solution. SOLBERG RE-HEALING RF3x6 FP ATC foam is compatible with most dry powder (chemical) agents.

## PERFORMANCE

### Fire Performance

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate has been tested to and meets the fire performance test criteria of European Standard EN 1568 Part 3 & 4 (latest edition) and International Maritime Organization (IMO) MSC.1/Circ.1312 (latest edition).

### Foam Proportioning

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate can be proportioned at the proper foam solution percentage using common foam proportioning devices such as:

- Eductors
- Inline balanced pressure proportioners
- Ratio controllers
- Self-educting nozzles



## DESCRIPTION

### SOLBERG® RE-HEALING™ RF3x6 Freeze Protected (FP) ATC™ foam concentrate

from SOLBERG® is an innovative environmentally sustainable fluorosurfactant and fluoropolymer-free foam concentrate used to effectively extinguish Class B hydrocarbon fuel fires at 3% and polar solvent fuel fires at 6% solution. SOLBERG RE-HEALING RF3x6 FP ATC foam can be used in fresh, salt or brackish water. SOLBERG RE-HEALING RF3x6 FP ATC foam possesses excellent burn back resistance due to its remarkable flow and rapid resealing characteristics. RE-HEALING foam concentrates are formulated using a new high performance synthetic foam technology to replace traditional AFFF, FFFP foam concentrates and older protein and fluoroprotein foams.

## STORAGE

The storage temperature range for SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate is 0°F to 120°F (-18°C to 50°C).

When stored in original containers or in manufacturer recommended equipment and within the specified temperature range, the shelf life is 20 years.

## COMPATIBILITY

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate should not be mixed with other foam concentrates. For questions about compatibility or mixing, consult Solberg Technical Services.

### Materials of Construction Capability

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate is compatible with multiple materials of construction such as carbon steel, stainless steel, brass, polyethylene and PVC. Galvanized steel should not be used in direct contact with the foam concentrate. For questions about materials of construction compatibility, consult Solberg Technical Services.

## INSPECTION

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate or pre-mix solution should be inspected annually per National Fire Protection Association (NFPA) Standards 11 and 25. A sample of the foam concentrate should be sent to the manufacturer for quality conditioning testing in accordance to NFPA 11.

# SOLBERG® RE-HEALING™ RF3X6% FREEZE PROTECTED ATC™ FOAM CONCENTRATE

## ENVIRONMENTAL INFORMATION

SOLBERG RE-HEALING foam concentrates are fluorosurfactant, fluoropolymer-free products for use on Class B hydrocarbon fuels with no environmental concerns for persistence, bioaccumulation or toxic break down.

## CERTIFICATIONS

SOLBERG manufactured products are thoroughly inspected and undergo rigorous quality control tests. These evaluations analyze the foam's physical parameters as well as the finished product's fire performance. A Certificate of Analysis (CoA) is issued with every batch.

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate is European Standard EN 1568 Part 3 & 4 Approved, International Maritime Organization (IMO) MSC.1/Circ.1312 Approved and meets the quality and performance test requirements of LASTFIRE.

## ORDERING INFORMATION

SOLBERG RE-HEALING RF3x6 FP ATC foam concentrate is available in pails, drums, totes and bulk quantities.

| Part No. | Description                                                   | Approximate Shipping Weight | Approximate Cube                             |
|----------|---------------------------------------------------------------|-----------------------------|----------------------------------------------|
| 20280    | SOLBERG RE-HEALING RF3x6 FP ATC, 5 gallon (20 litre) pail     | 45 lb (21 kg)               | 1.25 ft <sup>3</sup> (0.04 m <sup>3</sup> )  |
| 20281    | SOLBERG RE-HEALING RF3x6 FP ATC, 55 gallon (200 litre) drum   | 495 lb (224 kg)             | 11.83 ft <sup>3</sup> (0.33 m <sup>3</sup> ) |
| 20282    | SOLBERG RE-HEALING RF3x6 FP ATC, 265 gallon (1000 litre) tote | 2465 lb (1118 kg)           | 50.05 ft <sup>3</sup> (1.42 m <sup>3</sup> ) |
| 20283    | SOLBERG RE-HEALING RF3x6 FP ATC, bulk                         | Call Customer Services      |                                              |



## Solutions That Save.

### FOR MORE INFORMATION

Contact any of our worldwide Perimeter Solutions Fire Safety offices or visit:

[www.Perimeter-Solutions.com](http://www.Perimeter-Solutions.com)

### UNITED STATES

10667 Jersey Blvd.  
Rancho Cucamonga, CA 91730

Tel: +1 800 682 3626  
Tel: +1 909 983 0772

[salesfoamusa@perimeter-solutions.com](mailto:salesfoamusa@perimeter-solutions.com)

### EMEA

Polígono de Baiña, Parcela 23  
33682 Mieres (Asturias)  
Spain

Tel: +34 985 24 29 45

[salesfoamemea@perimeter-solutions.com](mailto:salesfoamemea@perimeter-solutions.com)

### ASIA PACIFIC

3 Charles Street  
St Marys NSW 2760 – Australia

Tel: +61 2 9673 5300

[salesfoamapac@perimeter-solutions.com](mailto:salesfoamapac@perimeter-solutions.com)

[perimeter-solutions.com](http://perimeter-solutions.com)

**NOTICE** PERIMETER SOLUTIONS MAKES NO REPRESENTATIONS OR WARRANTIES AS TO THE COMPLETENESS OR ACCURACY OF THE INFORMATION INCLUDED HEREIN. THE INFORMATION CONTAINED HEREIN IS NOT INTENDED TO PROVIDE REGULATORY, LEGAL OR EXPERT ADVICE RELATING TO THE PRODUCTS, ITS APPLICATION OR USES. NOTHING CONTAINED HEREIN IS TO BE CONSTRUED AS A RECOMMENDATION TO USE ANY PRODUCT, PROCESS, EQUIPMENT OR FORMULATION IN CONFLICT WITH ANY INDUSTRIAL PROPERTY OR INTELLECTUAL PROPERTY RIGHTS, AND PERIMETER SOLUTIONS MAKES NO REPRESENTATION OR WARRANTY, EXPRESS OR IMPLIED, THAT THE USE THEREOF WILL NOT INFRINGE ON ANY INDUSTRIAL PROPERTY OR INTELLECTUAL PROPERTY RIGHTS. NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESSED OR IMPLIED, OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE ARE MADE HEREUNDER WITH RESPECT TO THE INFORMATION CONTAINED HEREIN.