

# SOLBERG® RE-HEALING™ RFI-AG, 1% FOAM CONCENTRATE



## TYPICAL PHYSICAL PROPERTIES AT 77 °F (25 °C)

**Appearance:** Clear, yellow-orange liquid

**Freezing Point:** -11°F (-24°C)  
(No quality loss after thawing)

**Maximum Storage Temp:** 122°F (50°C)

**pH:** 7.0 - 8.5

**Refractive Index:** 1.4040 – 1.4110

**Specific Gravity:** 1.110 – 1.130

**Viscosity:** < 20 cSt\*

**Sediments:** < 0.05%

\*Cannon-Fenske Viscometer



## APPLICATIONS

SOLBERG RE-HEALING RFI-AG foam concentrate is intended for use on Class B hydrocarbon fuel fires. It is not intended for use on Class B polar solvent fuels. The foam can be used to prevent re-ignition of a liquid spill and control hazardous vapors. On Class A fuels, SOLBERG RE-HEALING RFI-AG foam will improve extinguishment in deep-seated fires. Foam discharge devices such as air aspirating, as well as non-air aspirating equipment can be used to obtain maximum results. The product is mixed 1 part foam concentrate to 99 parts water. It may also be used as a 1% pre-mix solution. SOLBERG RE-HEALING RFI-AG foam is compatible with most dry powder (chemical) agents.

## PERFORMANCE

### Fire Performance

SOLBERG RE-HEALING RFI-AG foam concentrate has been tested to and meets the fire performance test criteria of European Standard EN 1568 Part 3 (latest edition).

### Foam Proportioning

SOLBERG RE-HEALING RFI-AG foam concentrate can be proportioned at the proper foam solution percentage using common foam proportioning devices such as:

- Eductors
- Inline balanced pressure proportioners
- Ratio controllers
- Self-educing nozzles

## DESCRIPTION

**SOLBERG® RE-HEALING™ RFI-AG, 1% foam concentrate** from SOLBERG is an innovative environmentally sustainable fluorosurfactant and fluoropolymer-free foam concentrate used to effectively extinguish Class B hydrocarbon fuel fires. Proportioned at 1% solution, SOLBERG RE-HEALING RFI-AG foam concentrate can be used in fresh and salt water. SOLBERG RE-HEALING RFI-AG foam concentrate possesses excellent burn back resistance due to its remarkable flow and rapid resealing characteristics. SOLBERG RE-HEALING RFI-AG foam concentrate is formulated using a new high performance synthetic foam technology to replace traditional AFFF, FFFP foam concentrates and older protein and fluoroprotein foams.

## STORAGE

The storage temperature range for SOLBERG RE-HEALING RFI-AG foam concentrate is -11°F to 122°F (-24°C to 50°C). When stored in original containers or in manufacturer recommended equipment and within the specified temperature range, the shelf life is 20 years. Consult Solberg's Foam Storage Guidelines for further information.

## COMPATIBILITY

SOLBERG RE-HEALING RFI-AG foam concentrate should not be mixed with other foam concentrates. For questions about compatibility or mixing, consult Perimeter Solutions Technical Services.

### Materials of Construction Capability

SOLBERG RE-HEALING RFI-AG foam concentrate is compatible with multiple materials of construction such as carbon steel, stainless steel, brass, polyethylene and PVC. Galvanized steel should not be used in direct contact with the foam concentrate. For questions about materials of construction compatibility, consult Perimeter Solutions Technical Services.

## INSPECTION

SOLBERG RE-HEALING RFI-AG foam concentrate or pre-mix solution should be inspected annually per National Fire Protection Association (NFPA) Standards 11 and 25. A sample of the foam concentrate should be sent to the manufacturer for quality conditioning testing in accordance to NFPA 11.

# SOLBERG® RE-HEALING™ RFI-AG, 1% FOAM CONCENTRATE

## ENVIRONMENT INFORMATION

SOLBERG RE-HEALING is siloxane-free and contains no intentionally added PFAS chemicals, including PFOA and PFOS. Presenting no concern for persistence, bioaccumulation and is readily biodegradable.

## CERTIFICATION

SOLBERG manufactured products are thoroughly inspected and undergo rigorous quality control tests. These evaluations analyze the foam's physical parameters as well as the finished product's fire performance. A Certificate of Analysis (CoA) is issued with every batch. SOLBERG RE-HEALING RFI-AG foam concentrate is European Standard EN 1568 Part 3 Approved.

## ORDERING INFORMATION

SOLBERG RE-HEALING RFI-AG foam concentrate is available in pails, drums, totes and bulk quantities.

Part No.	Description	Approximate Shipping Weight	Approximate Cube
20840	SOLBERG RE-HEALING RFI-AG, 1% - 5 gallon (20 litre) pail	45 lb (21 kg)	1.25 ft <sup>3</sup> (0.04 m <sup>3</sup> )
20841	SOLBERG RE-HEALING RFI-AG, 1% - 55 gallon (200 litre) drum	495 lb (224 kg)	11.83 ft <sup>3</sup> (0.33 m <sup>3</sup> )
20842	SOLBERG RE-HEALING RFI-AG, 1% - 265 gallon (1000 litre) tote	2465 lb (1118 kg)	50.05 ft <sup>3</sup> (1.42 m <sup>3</sup> )
20843	SOLBERG RE-HEALING RFI-AG, 1% - bulk	Call Customer Services	



**Solutions That Save.**

### FOR MORE INFORMATION

Contact any of our worldwide Perimeter Solutions Fire Safety offices or visit:

[www.Perimeter-Solutions.com](http://www.Perimeter-Solutions.com)

### UNITED STATES

10667 Jersey Blvd.  
Rancho Cucamonga, CA 91730  
Tel: +1 (920) 593-9445  
[salesfoamusa@perimeter-solutions.com](mailto:salesfoamusa@perimeter-solutions.com)

### EMEA

Polígono Industrial de Baiña, Parcela 23  
33682 Baiña-Mieres (Asturias) – Spain  
Tel: +34 985 24 29 45  
[salesfoamemea@perimeter-solutions.com](mailto:salesfoamemea@perimeter-solutions.com)

### ASIA PACIFIC

3 Charles Street  
St Marys NSW 2760 – Australia  
Tel: +61 2 9673 5300  
[salesfoamapac@perimeter-solutions.com](mailto:salesfoamapac@perimeter-solutions.com)

[perimeter-solutions.com](http://perimeter-solutions.com)

**NOTICE** PERIMETER SOLUTIONS MAKES NO REPRESENTATIONS OR WARRANTIES AS TO THE COMPLETENESS OR ACCURACY OF THE INFORMATION INCLUDED HEREIN. THE INFORMATION CONTAINED HEREIN IS NOT INTENDED TO PROVIDE REGULATORY, LEGAL OR EXPERT ADVICE RELATING TO THE PRODUCTS, ITS APPLICATION OR USES. NOTHING CONTAINED HEREIN IS TO BE CONSTRUED AS A RECOMMENDATION TO USE ANY PRODUCT, PROCESS, EQUIPMENT OR FORMULATION IN CONFLICT WITH ANY INDUSTRIAL PROPERTY OR INTELLECTUAL PROPERTY RIGHTS, AND PERIMETER SOLUTIONS MAKES NO REPRESENTATION OR WARRANTY, EXPRESS OR IMPLIED, THAT THE USE THEREOF WILL NOT INFRINGE ON ANY INDUSTRIAL PROPERTY OR INTELLECTUAL PROPERTY RIGHTS. NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESSED OR IMPLIED, OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE ARE MADE HEREUNDER WITH RESPECT TO THE INFORMATION CONTAINED HEREIN.